

DTU324NRB

Safety switch, double throw, non fusible, 200A,
240 VAC/250 VDC, 3 poles, 15 hp, neutral,
NEMA 3R, bolt on



Main

Product	Double Throw Safety Switch
Duty Rating	General duty
Disconnect Type	Non-fusible disconnect switch
Factory Installed Neutral	Neutral (factory installed)
Number of Poles	3
Current Rating	200 A
Voltage Rating	240 V AC 250 V DC
Enclosure Rating	NEMA 3
Maximum Horse Power Rating	15 hp 240 V at AC 50-60 Hz for 3 phase conforming to NEC 240.6

Complementary

Short-circuit current	10 kA H or K
Fuse type	H or K
Mounting Type	Surface
Wire Size	AWG 6...300 kcmil copper or aluminium
Tightening torque	340 lbf.in (38.41 N.m) (AWG 6...300 kcmil)
Depth	10.63 in (270.00 mm)
Width	26.25 in (666.75 mm)
Height	32.5 in (825.50 mm)
Product Weight	78.00 lb(US) (35.38 kg)

Environment

Certifications	UL Listed
----------------	-----------

Ordering and shipping details

Category	00133 - DT SWITCH,NEMA3R
Discount Schedule	DE1
GTIN	785901185901
Nbr. of units in pkg.	1
Package weight(Lbs)	81.96 lb(US) (37.176 kg)
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	11.00 in (27.94 cm)
Package 1 width	26.30 in (66.802 cm)
Package 1 Length	34.00 in (86.36 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------