

EZM113125X

Branch unit, EZ Meter-Pak, 125A, 3 x 4 jaw sockets, 120/240VAC, no bypass, ringed, 1200A Al/Cu busbar

Main

Product	Meter Center Branch Unit
Current Rating	125 A
Type	Meter-Pak
Bus Rating	1200 A
Number of Jaws	4 without jaw release
Number of Meter Sockets	3
Bypass Type	No bypass
Socket Type	Ringed

Complementary

Certifications	UL Listed
Busbar Material	Aluminium/copper: busbar
Enclosure Material	Steel
Enclosure Rating	NEMA 3R
Maximum Voltage Rating	120/240 V AC
Mounting	Surface
Phase	1 phase in 1 phase out
Wire Configuration	3-wire
Height	42.37 in (1076.20 mm)
Width	12.25 in (311.15 mm)
Depth	7.09 in (180.09 mm)

Ordering and shipping details

Category	US10DE400020
Discount Schedule	0DE4
GTIN	785901373568
Returnability	No
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	42.4 in (107.6 cm)
Package 1 Width	12.2 in (31.1 cm)
Package 1 Length	7.09 in (18 cm)
Package 1 Weight	10.0002 lb(US) (4.536 kg)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes

Contractual warranty

Warranty	18 months
----------	-----------