

# EZMR313125X

Branch unit, EZ Meter-Pak, 125A, 3 x 5 jaw sockets, 208Y/120VAC, no bypass, ringless, 1200A Al/Cu busbar



## Main

Product	Meter Center Branch Unit
Current Rating	125 A
Type	Meter-Pak
Bus Rating	1200 A
Number of Jaws	5 without jaw release
Number of Meter Sockets	3
Bypass Type	No bypass
Socket Type	Ringless

## Complementary

Certifications	UL Listed
Busbar Material	Aluminium/copper: busbar
Enclosure Material	Steel
Enclosure Rating	NEMA 3R
Maximum Voltage Rating	208Y/120 V AC
Mounting	Surface
Phase	3 phase in 1 phase out
Wire Configuration	4-wire
Height	42.37 in (1076.20 mm)
Width	12.25 in (311.15 mm)
Depth	8.09 in (205.49 mm)

## Ordering and shipping details

Category	US10DE400020
Discount Schedule	0DE4
GTIN	785901373841
Returnability	No

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	42.4 in (107.6 cm)
Package 1 Width	12.2 in (31.1 cm)
Package 1 Length	8.07 in (20.5 cm)
Package 1 Weight	10.0002 lb(US) (4.536 kg)

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations

## Contractual warranty

Warranty	18 months
----------	-----------