

Main

Range	TeSys
Device short name	GS2AP
Product or Component Type	Terminal shroud
Accessory / separate part category	Protection accessory
Range compatibility	TeSys TeSys GS GS2QU
Standards	UL CSA
Poles description	3P
Switch rated current	400 A




Ordering and shipping details

Category	US10I1122640
Discount Schedule	0I11
GTIN	3606480512421
Returnability	Yes
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.76 in (7.0 cm)
Package 1 Width	6.69 in (17.0 cm)
Package 1 Length	8.27 in (21.0 cm)
Package 1 Weight	8.9 oz (253.0 g)
Unit Type of Package 2	S03
Number of Units in Package 2	13
Package 2 Height	11.81 in (30.0 cm)
Package 2 Width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	8.214 lb(US) (3.726 kg)

Offer Sustainability

Packaging without single use plastic	No
Packaging made with recycled cardboard	No
California proposition 65	WARNING: This product can expose you to chemicals including: Styrene, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes

China RoHS Regulation

 [China RoHS Declaration](#)

Take-back

No

Contractual warranty

Warranty

18 months
