



Main

Range	TeSys
Product name	TeSys GS
Device short name	GS2MU
Product or Component Type	Switch-disconnector-fuse
Device Application	Protection
Poles description	3P
Protected poles description	3t
Contacts type and composition	3 NO
[I _{th}] conventional free air thermal current	200 A (at 104 °F (40 °C))
[I _e] rated operational current	200 A
Fuse type	UL
Fuse size	J
Network type	DC AC
Network Frequency	50/60 Hz

Complementary

Type of operating handle	External frontal
Mounting Support	Plate
[U _i] rated insulation voltage	750 V
[U _{imp}] rated impulse withstand voltage	8 kV
Rated operational power in W	100 kW 400 V 140 kW 500 V 185 kW 690 V
Breaking capacity	1600 A 400 V
Short-circuit withstand	200 kA
Mechanical durability	10000 cycles
Electrical durability	6000 cycles
Connections - terminals	Power circuit lugs-ring terminals 0.02...0.24 in ² (16...152 mm ²)
[I _{cm}] rated short-circuit making capacity	2 kA 400 V
Tightening torque	Power circuit 75.23 lbf.in (8.5 N.m)

Environment

Standards	UL98 CSA C22.2 No 4
IP degree of protection	IP20 IEC 60529 with terminal cover)
Ambient air temperature for operation	-4...158 °F (-20...70 °C)
Ambient Air Temperature for Storage	-40...176 °F (-40...80 °C)
Fire resistance	1760 °F (960 °C) body
Height	7.68 in (195 mm)
Width	7.72 in (196.2 mm)
Depth	5.12 in (130 mm)

Ordering and shipping details

Category	US10I1122640
Discount Schedule	0I11
GTIN	3606480512360
Returnability	Yes
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.71 in (14.500 cm)
Package 1 Width	9.65 in (24.500 cm)
Package 1 Length	12.60 in (32.000 cm)
Package 1 Weight	7.78 lb(US) (3.530 kg)
Unit Type of Package 2	S04
Number of Units in Package 2	3
Package 2 Height	11.81 in (30.000 cm)
Package 2 Width	15.75 in (40.000 cm)
Package 2 Length	23.62 in (60.000 cm)
Package 2 Weight	24.85 lb(US) (11.270 kg)
Unit Type of Package 3	P06
Number of Units in Package 3	12
Package 3 Height	29.53 in (75.000 cm)
Package 3 Width	23.62 in (60.000 cm)
Package 3 Length	31.50 in (80.000 cm)
Package 3 Weight	122.00 lb(US) (55.336 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Styrene, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information