

HEPD25W

Surge protection device, HEPD, 25kA, 120/240 V, 1 phase, 3 wire, SPD type 1, wholesale



Main

Product	Surge protection device
Range	Square D
Device Short Name	HEPD

Complementary

Voltage Rating	120/240 V AC
MCOV	150 V
SCCR	22 kA
Surge Current	25 kA per phase
Voltage Protection Rating	600 V L-N
Nominal Discharge Current	10 kA
Number of Phases	1 phase
Wiring Configuration	3-wire (isolated ground)
Local Signalling	1 LED green normal operation
Product destination	Load center
Type of Packing	Wholesale
Height	2.45 in (62.23 mm)
Width	2.89 in (73.41 mm)
Depth	2.06 in (52.32 mm)

Environment

Enclosure Rating	NEMA 4X
------------------	---------

Ordering and shipping details

Category	US1DE1B08461
Discount Schedule	DE1B
GTIN	785901479758
Returnability	Yes
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.30 in (8.382 cm)
Package 1 Width	4.10 in (10.414 cm)
Package 1 Length	5.60 in (14.224 cm)
Package 1 Weight	18.08 oz (512.565 g)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes