

HMIWRT100

Web viewer run time entity license,
EcoStruxure Operator Terminal Expert



Main

Range of Product	EcoStruxure Operator Terminal Expert
Product or Component Type	License
Format	Paper
Software Type	Add-on
Type of License	Node locked license
Variant	Runtime
Software Version	V3.5
Operating system requirement	Windows 10 64 bit
System Requirements	8 GB RAM 30 GB hard-drive space
User Language	English Italian Chinese Spanish French German Portuguese Korean

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Complementary

License category	Permanent
Communication port protocol	CANopen slave Couzet Automation millenium 3 FBD Emerson Industrial Automation Modbus SIO master Emerson Industrial Automation Modbus TCP master Control Techniques Modbus SIO master Control Techniques Modbus TCP master Modbus SIO master Emerson Process Management ROC Plus Ethernet Emerson Process Management ROC SIO HTTP IPsec Mitsubishi A series Ethernet Mitsubishi FX series CPU direct Mitsubishi FX series Ethernet Mitsubishi iQ-R/F series Ethernet SLMP client Mitsubishi Q series CPU direct Mitsubishi Q series QnU CPU Ethernet Mitsubishi Q/QnA series serial Modbus Organization Modbus SIO ASCII master Modbus Organization Modbus SIO master Modbus Organization Modbus SIO slave Modbus Organization Modbus TCP master Modbus Organization Modbus TCP slave Omron CS/CJ/CP series host link Omron CS/CJ/CP/NX series Ethernet Omron CS/CJ/NJ/NX series Ethernet/IP OPC UA server Profibus DP slave Rockwell Automation EtherNet/IP Rockwell Automation DF1 Rockwell Automation DH485 Schneider Electric Modbus SIO master Schneider Electric Modbus TCP master Schneider Electric Modbus TCP master via USB EtherNet/IP Schneider Electric Machine expert network DF1 Schneider Electric PacDrive Schneider Electric Uni-Telway Schneider Electric Zelio Logic DH485 Siemens Simatic S7 Ethernet Siemens Simatic S7 MPI direct Siemens TIA portal Ethernet websocket
Previous software version	V3.4
Software Function	Web viewer Alarms and events Blockly script Convertors Import export with CSV, tab and period delimiter Data and operation logging Multi language development Multi language tables Object binding and properties Target binding and properties Recipes Screens (contents and folders) Security (levels, project, users) System keypad Text script Color themes Variable (arrays, binding, properties, structures) OPC UA Server
Product Compatibility	Windows compatible PC
Range Compatibility	Harmony GTU Harmony GTUX Harmony ST6 Harmony STM6 Harmony STO7 Harmony iPC
Hosting option	On-device
License size	Entity (100 station)

Processor requirement	Intel core i3 8th generation Intel core i5 8th generation
Display resolution	320 x 240 pixels HVGA minimum 3840 x 2160 pixels 4K UHD maximum

Ordering and shipping details

Category	US10MC222569
Discount Schedule	0MC2
GTIN	3606481053992
Returnability	Yes
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.08 in (0.2 cm)
Package 1 Width	6.89 in (17.5 cm)
Package 1 Length	9.84 in (25.0 cm)
Package 1 Weight	0.19 oz (5.5 g)