



## Main

Product	Single Throw Safety Switch
Duty Rating	Heavy duty
Device Application	Heavy application
Disconnect Type	Non-fusible disconnect
Factory Installed Neutral	None
Phase	3 phase
Number of Poles	3
Current Rating	60 A
Voltage Rating	600 V AC/DC
Enclosure Rating	NEMA 1 steel
Motor power hp	10 Hp at 240 V AC 50-60 Hz for 1 phase motors 20 Hp at 240 V AC 50-60 Hz for 3 phase motors 25 Hp at 480 V AC 50-60 Hz for 1 phase motors 50 Hp at 480 V AC 50-60 Hz for 3 phase motors 30 Hp at 600 V AC 50-60 Hz for 1 phase motors 60 Hp at 600 V AC 50-60 Hz for 3 phase motors 10 Hp at 250 V DC 30 hp at 600 V DC

## Complementary

Mounting Type	Surface
Electrical Connection	Lugs
Wiring configuration	3-wire
Wire Size	AWG 14...AWG 3 copper AWG 12...AWG 3 aluminium
Tightening torque	50 Lbf.In (5.6 N.m) (AWG 3) 45 Lbf.In (5.08 N.m) (AWG 6...AWG 4) 40 Lbf.In (4.5 N.m) 0.013 in <sup>2</sup> (8.367 mm <sup>2</sup> ) (AWG 8) 50 lbf.in (5.6 N.m) 0.003...0.008 in <sup>2</sup> (2.06...5.261 mm <sup>2</sup> ) (AWG 14...AWG 10)
Depth	6.38 in (162.05 mm)
Width	10.5 in (266.7 mm)
Height	21.25 in (539.75 mm)
Net Weight	15.4 lb(US) (7 kg)

## Environment

Certifications	UL listed file E2875
----------------	----------------------

## Ordering and shipping details

Category	US10DE100008
Discount Schedule	0DE1
GTIN	785901505808
Returnability	Yes
Country of origin	US

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.400 in (18.796 cm)
Package 1 Width	10.800 in (27.432 cm)
Package 1 Length	19.800 in (50.292 cm)
Package 1 Weight	14.800 lb(US) (6.713 kg)
Unit Type of Package 2	PAL
Number of Units in Package 2	40
Package 2 Height	40.50 in (102.87 cm)
Package 2 Width	40.0000000000 in (101.6 cm)
Package 2 Length	48.0000000000 in (121.92 cm)
Package 2 Weight	620.000 lb(US) (281.227 kg)

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
PVC free	Yes

## Contractual warranty

Warranty	18 months
----------	-----------