



Main

Product or Component Type	Circuit breaker
Trip Unit Technology	Thermal-magnetic

Complementary

Line Rated Current	350 A
Number of Poles	3P
Breaking capacity code	A
Mounting Mode	I-Line
Wiring Configuration	3-wire
Magnetic Hold Current	1750 A
Magnetic Tripping Current	3500 A
Electrical connection	Lugs, load I-Line connection, line
Terminal identifier	AL400LA
Phase connection	ABC
Height	11 in (279.40 mm)
Width	6 in (152.40 mm)
Depth	5.84 in (148.34 mm)
Circuit breaker application	HACR rated

Environment

Certifications	UL Listed[RETURN]CSA
----------------	----------------------

Ordering and shipping details

Category	US10DE201040
Discount Schedule	0DE2
GTIN	785901426288
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.09 in (23.1 cm)
Package 1 Width	11.50 in (29.2 cm)
Package 1 Length	17.40 in (44.2 cm)
Package 1 Weight	18.39 lb(US) (8.34 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
PVC free	Yes
Halogen content performance	Halogen free plastic parts product

Contractual warranty

Warranty	18 months
----------	-----------