



Main

Product or Component Type	Terminal extension
Product Compatibility	LC1G265...500

Complementary

Poles description	3P
Height	5.79 in (147 mm)
Width	1.26 in (32 mm)
Depth	3.54 in (90 mm)
Net Weight	2.60 lb(US) (1.18 kg)
Quantity per Set	Set of 3

Environment

IP degree of protection	IP20 IEC 60529 with terminal shields)
Pollution degree	3 IEC 60947-1
Operating altitude	9842.52 ft (3000 m) without derating 5000 m with derating factor
Standards	EN/IEC 60947-4-1 UL 60947-4-1 CSA C22.2 No 60947-4-1 GB/T 14048.4
Ambient air temperature for operation	-13...140 °F (-25...60 °C)
Ambient Air Temperature for Storage	-76...176 °F (-60...80 °C)

Ordering and shipping details

Category	US10I1222328
Discount Schedule	0I12
GTIN	3606481916389
Returnability	No
Country of origin	CN

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.57 in (4.000 cm)
Package 1 Width	4.72 in (12.000 cm)
Package 1 Length	7.87 in (20.000 cm)

Package 1 Weight	2.59 lb(US) (1.177 kg)
Unit Type of Package 2	S02
Number of Units in Package 2	4
Package 2 Height	5.91 in (15.000 cm)
Package 2 Width	11.81 in (30.000 cm)
Package 2 Length	15.75 in (40.000 cm)
Package 2 Weight	11.42 lb(US) (5.180 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Styrene, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
PVC free	Yes
Halogen content performance	Halogen free plastic parts product