



Main

Range	TeSys
Device short name	LA9G
Product or Component Type	Set of connections
Accessory / separate part category	Connection accessory
Electrical circuit type	Star
Quantity per Set	Set of 1

Complementary

Poles description	3P
Product Compatibility	LC1G265...500 LC1G300...475C
Range compatibility	TeSys Giga
Height	3.19 in (81 mm)
Width	5.43 in (138 mm)
Depth	0.59 in (15 mm)
Net Weight	12.80 oz (363 g)

Environment

Standards	EN/IEC 60947-4-1
Ambient Air Temperature for Storage	-76...176 °F (-60...80 °C)
Operating altitude	9842.52 ft (3000 m) without derating 5000 m with derating factor

Ordering and shipping details

Category	US10I1222329
Discount Schedule	0I12
GTIN	3606485827810
Returnability	Yes
Country of origin	CN

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.59 in (1.5 cm)
Package 1 Width	3.19 in (8.1 cm)
Package 1 Length	5.43 in (13.8 cm)
Package 1 Weight	15.63 oz (443 g)
Unit Type of Package 2	S02
Number of Units in Package 2	8
Package 2 Height	5.91 in (15 cm)
Package 2 Width	11.81 in (30 cm)

Package 2 Length	15.75 in (40 cm)
Package 2 Weight	8.95 lb(US) (4.059 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Styrene, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information