

# Product data sheet

## Characteristics

# LDB123

Wireway, Square-Duct, 12 inch by 12 inch, 3 feet long, hinged cover, N1 paint, NEMA 1

### Main

Product	Straight length
Range	SQUARE-Duct
Length	3 ft (0.9 m)
Cross Section	12 x 12 in
Enclosure Rating	NEMA 1
Enclosure Material	Steel 14 gauge without knock-outs
Finish	Gray polyester powder ANSI 49
Cover Type	Hinged cover
Certifications	UL Listed[RETURN]CSA

### Ordering and shipping details

Category	US10PE901421
Discount Schedule	0PE9
GTIN	785901095460
Returnability	Yes
Country of origin	MX

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	13.00 in (33.02 cm)
Package 1 Width	13.00 in (33.02 cm)
Package 1 Length	37.400 in (94.996 cm)
Package 1 Weight	39.00 lb(US) (17.69 kg)

### Offer Sustainability

REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>

### Contractual warranty

Warranty	18 months
----------	-----------

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.