



### Main

Product or Component Type	Full voltage starter
Range of Product	Instakits
Motor starter type	Non reversing
Disconnecter device type	PowerPact motor circuit protector

### Complementary

[Ue] rated operational voltage	120 V AC 50/60 Hz
[Ie] rated operational current AC	18 A
Maximum Horse Power Rating	25 Hp 575 V AC, 3 phase 5 Hp 208 V AC, 3 phase 5 Hp 230 V AC, 3 phase 10 hp 460 V AC, 3 phase
[Uc] control circuit voltage	600 V AC
Auxiliary contact composition	1 NO + 1 NC
Protection Type	Motor circuit protector 30 A
Location of connection	Line

### Environment

Product Certifications	IEC[RETURN]CSA[RETURN]UL
NEMA degree of protection	NEMA 12 steel

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
PVC free	Yes