



Main

Range	Lineryg
Product name	Lineryg DS
Product or Component Type	Distribution block

Complementary

Mounting Support	DIN rail
Range compatibility	Prisma G Prisma P Prisma PH Prisma Pack Spacial Kaedra Pragma TeSys
Product Compatibility	Spacial enclosures
Poles description	1P
Distribution block outgoing	13 holes
[Ue] rated operational voltage	230 V AC Ph/N 440 V AC Ph/Ph
[Ui] rated insulation voltage	500 V AC
[Uimp] rated impulse withstand voltage	8 kV
[Ie] rated operational current	160 A 104 °F (40 °C)
[Icw] rated short-time withstand current	8.4 kA 1 s
[Ipk] rated peak withstand current	36 kA
Connections - terminals	Supply screw terminal 2 0.04...0.11 in ² (25...70 mm ²) rigid Supply screw terminal 2 0.02...0.08 in ² (16...50 mm ²) flexible with cable end Distribution screw terminal 3 0.00...0.04 in ² (2.5...25 mm ²) rigid Distribution screw terminal 3 0.00...0.02 in ² (1.5...16 mm ²) flexible with cable end Distribution screw terminal 8 0.00...0.02 in ² (1.5...16 mm ²) rigid Distribution screw terminal 8 0.00...0.02 in ² (1.5...10 mm ²) flexible with cable end
Tightening torque	Distribution 17.70 lbf.in (2 N.m) flat 0.30 in (7.5 mm) Distribution 17.70 lbf.in (2 N.m) PZ2 0.30 in (7.5 mm) Distribution 17.70 lbf.in (2 N.m) flat 0.23 in (5.8 mm) Distribution 17.70 lbf.in (2 N.m) PZ2 0.23 in (5.8 mm) Supply 79.66 lbf.in (9 N.m) flat 0.47 in (12 mm) Supply 79.66 lbf.in (9 N.m) PZ2 0.47 in (12 mm)
9 mm pitches	4
Height	3.35 in (85 mm)
Width	1.42 in (36 mm)
Depth	1.99 in (50.5 mm)
Net Weight	0.37 lb(US) (0.168 kg)
Color	White RAL 9003)

Environment

Pollution degree	3
Overvoltage category	III
Dielectric strength	2500 V
Standards	EN/IEC 60947-7-1 EN/IEC 61439-1
Ambient air temperature for operation	-13...131 °F (-25...55 °C)


Ordering and shipping details

Category	US10DE200908
Discount Schedule	0DE2
GTIN	3606480542169
Returnability	No
Country of origin	TN

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.05 in (5.200 cm)
Package 1 Width	1.97 in (5.000 cm)
Package 1 Length	3.54 in (9.000 cm)
Package 1 Weight	6.28 oz (178.000 g)
Unit Type of Package 2	S03
Number of Units in Package 2	60
Package 2 Height	11.81 in (30.000 cm)
Package 2 Width	11.81 in (30.000 cm)
Package 2 Length	15.75 in (40.000 cm)
Package 2 Weight	25.27 lb(US) (11.462 kg)
Unit Type of Package 3	P12
Number of Units in Package 3	480
Package 3 Height	17.72 in (45.000 cm)
Package 3 Width	31.50 in (80.000 cm)
Package 3 Length	47.24 in (120.000 cm)
Package 3 Weight	229.28 lb(US) (104.000 kg)

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------