



Main

Product or Component Type	Long terminal shield
Range compatibility	ComPacT new generation ComPacT NSX100 new generation ComPacT new generation ComPacT NSX160 new generation ComPacT new generation ComPacT NSX250 new generation ComPacT ComPacT NSX100 ComPacT ComPacT NSX160 ComPacT ComPacT NSX250 ComPacT new generation ComPacT NSX DC new generation NSX100 DC ComPacT new generation ComPacT NSX DC new generation NSX160 DC ComPacT new generation ComPacT NSX DC new generation NSX250 DC ComPacT Compact NSX100 DC ComPacT Compact NSX160 DC ComPacT Compact NSX250 DC EasyPact EasyPact CVS100 EasyPact EasyPact CVS160 EasyPact EasyPact CVS250
Accessory / separate part type	Insulation accessories
Poles description	3P
Quantity per Set	1

Complementary

Connection pitch	1.4 in (35 mm)
IP degree of protection	IP40 conforming to IEC 60529
Product Compatibility	Circuit-breaker Plug-in base

Ordering and shipping details

Category	US10DE201103
Discount Schedule	0DE2
GTIN	3606480019913
Returnability	No
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.150 in (8.000 cm)
Package 1 Width	3.543 in (9.000 cm)
Package 1 Length	5.118 in (13.000 cm)
Package 1 Weight	5.256 oz (149.000 g)
Unit Type of Package 2	S04
Number of Units in Package 2	56
Package 2 Height	11.811 in (30.000 cm)
Package 2 Width	15.748 in (40.000 cm)
Package 2 Length	23.622 in (60.000 cm)

Package 2 Weight	20.455 lb(US) (9.278 kg)
Unit Type of Package 3	P12
Number of Units in Package 3	224
Package 3 Height	17.717 in (45.000 cm)
Package 3 Width	31.496 in (80.000 cm)
Package 3 Length	47.244 in (120.000 cm)
Package 3 Weight	107.780 lb(US) (48.888 kg)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes

Contractual warranty

Warranty	18 months
----------	-----------