


LXD3T7

Contacteur coil, TeSys Deca, 480V AC 60Hz for D40A-D80A DT60A-DT80A contactor



Main

Range	TeSys
Product or Component Type	Contacteur coil
Device short name	LXD3
Control circuit type	AC 60 Hz
[Uc] control circuit voltage	480 V AC 60 Hz
Average resistance	607 Ohm 68 °F (20 °C)
Inductance of closed circuit	33.1 H
Product Compatibility	LC1D40A...D80A LC2D40A...D80A LC1DT60A...DT80A
Mechanical durability	6 Mcycles
Maximum operating rate	3600 cyc/h 140 °F (60 °C)

Complementary

Coil technology	Without built-in suppressor module
Control circuit voltage limits	Drop-out: 0.3...0.6 Uc at 60 Hz (at <140 °F (60 °C)) Operational: 0.85...1.1 Uc at 60 Hz (at <140 °F (60 °C))
Inrush power in VA	160 VA 60 Hz cos phi 0.75 (at 68 °F (20 °C))
Hold-in power consumption in VA	15 VA 60 Hz cos phi 0.3 (at 68 °F (20 °C))
Heat dissipation	4...5 W 60 Hz

Environment

Ambient air temperature for operation	23...140 °F (-5...60 °C)
Net Weight	0.15 lb(US) (0.07 kg)

Ordering and shipping details

Category	US10I1222341
Discount Schedule	0I12
GTIN	3389119410496
Returnability	Yes
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.28 in (5.8 cm)
Package 1 Width	2.28 in (5.8 cm)
Package 1 Length	3.86 in (9.8 cm)
Package 1 Weight	5.64 oz (160.0 g)
Unit Type of Package 2	S01
Number of Units in Package 2	12
Package 2 Height	5.91 in (15.0 cm)
Package 2 Width	5.91 in (15.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	4.73 lb(US) (2.145 kg)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------