



Main

Product	Surface cover
Color	Gray
Cover type	Surface cover

Complementary

Material	Steel
Maximum Width	20 in (508.00 mm)
Maximum Height	26 in (660.40 mm)
Tightening torque	Cover 10...12 lb.in

Environment

Enclosure Rating	NEMA 1
Product certifications	CULus

Ordering and shipping details

Category	08352 - NF / NQ TRIMS RTA
Discount Schedule	PE1A
GTIN	00785901798828
Nbr. of units in pkg.	1
Package weight(Lbs)	15.4 lb(US) (6.99 kg)
Returnability	Yes
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	2.00 in (5.08 cm)
Package 1 width	22.00 in (55.88 cm)
Package 1 Length	28.00 in (71.12 cm)
Unit Type of Package 2	PAL
Number of Units in Package 2	36
Package 2 Weight	527.00 lb(US) (239.043 kg)
Package 2 Height	39.00 in (99.06 cm)
Package 2 width	42.00 in (106.68 cm)
Package 2 Length	42.00 in (106.68 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------