



Main

Range	Spacial
Application	Outdoor heavy duty
Accessory / separate part category	Enclosure accessory
Product or Component Type	Side panel
Application	Multi-purpose
For enclosure nominal dimensions	- - H: 81.18 in (2062 mm) W: 31.50 in (800 mm) D: 16.93 in (430 mm)
Mounting Location	Sides of enclosure
Quantity per Set	Set of 1

Complementary

Range compatibility	Spacial Spacial SFHD
Device composition	Fixing elements 2 side panel
Material	Steel with anti-corrosive coating
Color	Gray RAL 7035)
Surface Finish	Epoxy-polyester powder
Fixing mode	By screws captive - from the inside of enclosure
Height	Nominal: 78.74 in (2000 mm)
Width	Nominal: 16.93 in (430 mm)
Depth	Real : 2.36 in (60 mm)

Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1
GTIN	3606480678493
Returnability	No
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.36 in (6.0 cm)
Package 1 Width	15.35 in (39.0 cm)
Package 1 Length	82.28 in (209.0 cm)
Package 1 Weight	47.16 lb(US) (21.39 kg)
Unit Type of Package 2	PAL
Number of Units in Package 2	30
Package 2 Height	29.53 in (75.0 cm)
Package 2 Width	82.68 in (210.0 cm)
Package 2 Length	47.24 in (120.0 cm)
Package 2 Weight	1538.83 lb(US) (698.0 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations