



## Main

|                                    |                            |
|------------------------------------|----------------------------|
| Range                              | Spacial                    |
| Product or Component Type          | Grommet                    |
| Accessory / separate part category | Cable management accessory |
| Device Application                 | Multi-purpose              |
| Quantity per Set                   | Set of 4                   |

## Complementary

|                    |                                 |
|--------------------|---------------------------------|
| Material           | TPE (thermoplastic elastomer)   |
| Cable entry number | 1 x 0.75...0.79 in (19...20 mm) |
| Net Weight         | 0.02 lb(US) (0.007 kg)          |

## Environment

|                                       |  |
|---------------------------------------|--|
| IP degree of protection               | IP65 conforming to IEC 60529   |
| Flame retardance                      | V0 conforming to UL 94   |
| Ambient air temperature for operation | -22...212 °F (-30...100 °C)  |
| Resistance to chemical agents         | Good resistance to mineral oils and greases<br>Good resistance to weak acids and bases<br>Good resistant to alcohols<br>Good resistance to fuels |

## Packing Units

|                              |                   |
|------------------------------|-------------------|
| Unit Type of Package 1       | PCE               |
| Number of Units in Package 1 | 1                 |
| Package 1 Height             | 1.18 in (3 cm)    |
| Package 1 Width              | 1.48 in (3.75 cm) |
| Package 1 Length             | 3.54 in (9 cm)    |
| Package 1 Weight             | 0.25 oz (7 g)     |
| Unit Type of Package 2       | BB1               |
| Number of Units in Package 2 | 4                 |
| Package 2 Height             | 1.18 in (3 cm)    |
| Package 2 Width              | 3.54 in (9 cm)    |
| Package 2 Length             | 5.91 in (15 cm)   |
| Package 2 Weight             | 0.99 oz (28 g)    |
| Unit Type of Package 3       | CAR               |
| Number of Units in Package 3 | 80                |
| Package 3 Height             | 7.87 in (20 cm)   |
| Package 3 Width              | 7.87 in (20 cm)   |
| Package 3 Length             | 11.81 in (30 cm)  |
| Package 3 Weight             | 26.17 oz (742 g)  |

## Offer Sustainability

|                            |   |
|----------------------------|---|
| Sustainable offer status   | Green Premium product   |
| REACH Regulation           | <a href="#"> REACH Declaration</a>             |
| EU RoHS Directive          | Pro-active compliance (Product out of EU RoHS legal scope)  |
| Mercury free               | Yes   |
| China RoHS Regulation      | <a href="#"> China RoHS Declaration</a>        |
| RoHS exemption information | <a href="#"> Yes</a>                           |
| Environmental Disclosure   | <a href="#"> Product Environmental Profile</a> |
| Circularity Profile        | No need of specific recycling operations  |