




Main

Range	Spacial
Product or Component Type	Grommet
Accessory / separate part category	Cable management accessory
Device Application	Multi-purpose
Quantity per Set	Set of 4

Complementary

Material	TPE (thermoplastic elastomer)
Cable entry number	1 x 0.83...0.87 in (21...22 mm)
Net Weight	0.01 lb(US) (0.005 kg)

Environment

IP degree of protection	IP65 conforming to IEC 60529
Flame retardance	V0 conforming to UL 94
Ambient air temperature for operation	-22...212 °F (-30...100 °C)
Resistance to chemical agents	Good resistance to fuels Good resistance to mineral oils and greases Good resistant to alcohols Good resistance to weak acids and bases

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.18 in (3 cm)
Package 1 Width	1.48 in (3.75 cm)
Package 1 Length	3.54 in (9 cm)
Package 1 Weight	0.18 oz (5 g)
Unit Type of Package 2	BB1
Number of Units in Package 2	4
Package 2 Height	1.18 in (3 cm)
Package 2 Width	3.54 in (9 cm)
Package 2 Length	5.91 in (15 cm)
Package 2 Weight	0.78 oz (22 g)
Unit Type of Package 3	CAR
Number of Units in Package 3	80
Package 3 Height	7.87 in (20 cm)
Package 3 Width	7.87 in (20 cm)
Package 3 Length	11.81 in (30 cm)
Package 3 Weight	21.09 oz (598 g)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations