




Main

Range	Spacial
Product or Component Type	Grommet
Accessory / separate part category	Cable management accessory
Device Application	Multi-purpose
Quantity per Set	Set of 12

Complementary

Material	TPE (thermoplastic elastomer)
Cable entry number	1 x 0.39...0.43 in (10...11 mm)
Net Weight	0.01 lb(US) (0.003 kg)

Environment

IP degree of protection	IP65 conforming to IEC 60529
Flame retardance	V0 conforming to UL 94
Ambient air temperature for operation	-22...212 °F (-30...100 °C)
Resistance to chemical agents	Good resistant to alcohols Good resistance to fuels Good resistance to weak acids and bases Good resistance to mineral oils and greases

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.18 in (3.0 cm)
Package 1 Width	1.48 in (3.75 cm)
Package 1 Length	3.54 in (9.0 cm)
Package 1 Weight	0.11 oz (3.0 g)
Unit Type of Package 2	BB1
Number of Units in Package 2	12
Package 2 Height	1.18 in (3.0 cm)
Package 2 Width	3.54 in (9.0 cm)
Package 2 Length	5.91 in (15.0 cm)
Package 2 Weight	1.48 oz (42.0 g)
Unit Type of Package 3	CAR
Number of Units in Package 3	240
Package 3 Height	7.87 in (20.0 cm)
Package 3 Width	7.87 in (20.0 cm)
Package 3 Length	11.81 in (30.0 cm)
Package 3 Weight	35.98 oz (1020.0 g)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations