



Main

Range	Spacial
Product or Component Type	Cable gland
Accessory / separate part category	Cable management accessory
Range compatibility	Spacial Spacial CRN Spacial Spacial S3D Spacial Spacial S3X
Mounting Location	Enclosure top Enclosure bottom
Cable entry	Cable gland M20
Device composition	1 cable gland 1 lock nut 1 seal
Quantity per Set	Set of 4
Material	Seal CR (chloroprene) Body stainless steel AISI 304L

Complementary

Color	Gray
Fixing mode	Screwed By nut
Height	1.42 in (36 mm)
Net Weight	0.07 lb(US) (0.034 kg)

Environment

Product Certifications	VDE
Flame retardance	V2 conforming to UL 94
Ambient Air Temperature for Operation	-4...212 °F (-20...100 °C) permanent -40...302 °F (-40...150 °C) intermittent
IP degree of protection	IP68 IEC 60529 5 bar, 30 min

Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1
GTIN	3606481360236
Returnability	No
Country of origin	TR

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.18 in (3 cm)
Package 1 Width	1.18 in (3 cm)
Package 1 Length	1.38 in (3.5 cm)
Package 1 Weight	1.38 oz (39 g)

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes