



## Main

Range	Spacial
Product or Component Type	Cable gland
Accessory / separate part category	Cable management accessory
Range compatibility	Spacial Spacial CRN Spacial Spacial S3D Spacial Spacial S3X
Mounting Location	Enclosure bottom Enclosure top
Cable entry	Cable gland M40
Device composition	1 cable gland 1 lock nut 1 seal
Quantity per Set	Set of 2
Material	Seal CR (chloroprene) Body stainless steel AISI 316L

## Complementary

Color	Gray
Fixing mode	Screwed By nut
Height	1.95 in (49.6 mm)
Net Weight	0.29 lb(US) (0.133 kg)

## Environment

Product Certifications	VDE
Flame retardance	V2 conforming to UL 94
Ambient Air Temperature for Operation	-4...212 °F (-20...100 °C) permanent -40...302 °F (-40...150 °C) intermittent
IP degree of protection	IP68 IEC 60529 5 bar, 30 min

## Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1
GTIN	3606481360328
Returnability	No
Country of origin	TR

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.77 in (4.5 cm)
Package 1 Width	1.77 in (4.5 cm)
Package 1 Length	1.97 in (5 cm)
Package 1 Weight	5.93 oz (168 g)

Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>