



#### Main

Range of Product	Actassi
Product or Component Type	19" front panel
Device Application	Multi-purpose Electronic application
Color	Gray RAL 7035)

#### Complementary

Mounting Location	On vertical uprights
Number of rack unit	1U
Mounting support	19" rack, front or rear
Product Compatibility	Spacial SF-S, SF-E, VDM, PLA enclosures Actassi enclosure
Material	Sheet steel
Surface Finish	Epoxy-polyester powder
Thickness	0.06 in (1.5 mm)
Fixing mode	By 19" fixing element 19" uprights of rack
Number of units 19"	1
Height	1.75 in (44.45 mm)
Width	18.31 in (465 mm)



#### Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1
GTIN	3606480173400
Returnability	No
Country of origin	US

#### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.39 in (1.0 cm)
Package 1 Width	1.77 in (4.5 cm)
Package 1 Length	19.09 in (48.5 cm)
Package 1 Weight	9.10 oz (258.0 g)
Unit Type of Package 2	P12
Number of Units in Package 2	600
Package 2 Height	17.72 in (45.0 cm)
Package 2 Width	31.50 in (80.0 cm)
Package 2 Length	47.24 in (120.0 cm)
Package 2 Weight	436.52 lb(US) (198.0 kg)

Offer Sustainability

REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 <a href="#">Yes</a>

Contractual warranty

Warranty	18 months
----------	-----------