



Main

Range	Thalassa
Accessory / separate part category	Connection accessory
Product or Component Type	Cable connector
Application	Cable installation
Additional information	With strain relief
Line Rated Current	16 A
Rated voltage	250 V
Network type	AC

Complementary

Connector Type	Female
Material	Polyamide
Body colour	Black
Fixing mode	Screw
Cable outer diameter	0.22...0.35 in (5.5...9 mm)
Nominal cross section	0.00...0.00 in ² (0.5...2.5 mm ²)
Cable cross section	0.00...0.00 in ² (0.5...2.5 mm ²)
Height	0.54 in (13.8 mm)
Width	0.91 in (23 mm)
Depth	2.09 in (53.2 mm)
IP degree of protection	IP20

Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1
GTIN	3606489550837
Returnability	No
Country of origin	DE

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.38 in (3.5 cm)
Package 1 Width	4.92 in (12.5 cm)
Package 1 Length	2.76 in (7.0 cm)
Package 1 Weight	0.18 oz (5.0 g)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information