



Main

Range of Product	Lighting and power sockets
Accessory / separate part category	Lighting accessory
Product or Component Type	Lamp
Device Application	Multi-purpose
Device composition	1 lamp 1 fixing elements
Power factor	0.9

Complementary

Outlet standard deviation	French
Rated lamp wattage	10 W
[Ue] rated operational voltage	230 V AC 50/60 Hz
Bulb base	Integral LED
Bulb type	LED
Control Type	Built-in switch
Luminous flux	950 lm
Colour temperature	4000 K
Service life in hours	25000 h
Electrical connection	Cable quick connector 9.84 ft (3 m) not supplied Cable quick connector 3.28 ft (1 m) not supplied
Mounting Support	Metal parts Bracket DIN rail
Fixing Mode	Screws Clip-in Magnetic fixing
Range compatibility	Spacial Thalassa
Material	PC (UL94 V-0)
Length	14.65 in (372 mm)
Height	2.48 in (63 mm)
Width	1.57 in (40 mm)
Color	Black RAL 9005)

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Environment

IP degree of protection	IP20 conforming to IEC 60529
Electrical Insulation Class	Class I
Electromagnetic compatibility	EMC immunity EN 55015
Standards	IEC 60598 UL 94 UL 508 A EN 55015 UL 1598 UL 8750
Ambient air temperature for operation	3...149 °F (-16...65 °C)
Ambient Air Temperature for Storage	14...140 °F (-10...60 °C)

Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1
GTIN	3606481203052
Returnability	No
Country of origin	CN

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.17 in (5.500 cm)
Package 1 Width	2.95 in (7.500 cm)
Package 1 Length	15.94 in (40.500 cm)
Package 1 Weight	30.34 oz (860.000 g)
Unit Type of Package 2	S04
Number of Units in Package 2	10
Package 2 Height	11.81 in (30.000 cm)
Package 2 Width	15.75 in (40.000 cm)
Package 2 Length	23.62 in (60.000 cm)
Package 2 Weight	19.43 lb(US) (8.814 kg)
Unit Type of Package 3	P12
Number of Units in Package 3	40
Package 3 Height	17.72 in (45.000 cm)
Package 3 Width	31.50 in (80.000 cm)
Package 3 Length	47.24 in (120.000 cm)
Package 3 Weight	104.18 lb(US) (47.256 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.