

Main

Product or Component Type	Pendant control station
Device short name	PBXA
Control station type	Double insulated

Complementary

Enclosure Material	Polypropylene
Control Type	Intuitive
Enclosure Type	Complete ready for use
Mechanical interlocking	With mechanical interlocking
Control station colour	Red
Ambient Air Temperature for Storage	-40...158 °F (-40...70 °C)
Mechanical durability	3000000 cycles
Cable entry	Rubber sleeve with stepped entry 0.3...1.2 in (7.5...29.5 mm)
[Ui] rated insulation voltage	2500 V
Contact operation	Snap action
Net Weight	0.93 lb(US) (0.42 kg)

Environment

Standards	NEMA 4X
Protective treatment	TH
Ambient Air Temperature for Operation	-13...158 °F (-25...70 °C)
Vibration resistance	15 gn 10...500 Hz)IEC 60068-2-6
IP degree of protection	IP65 conforming to IEC 60529

Ordering and shipping details

Category	US10CS222473
Discount Schedule	OCS2
GTIN	3606480422676
Returnability	No
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.740 in (9.500 cm)
Package 1 Width	2.047 in (5.200 cm)
Package 1 Length	11.614 in (29.500 cm)
Package 1 Weight	13.122 oz (372.000 g)
Unit Type of Package 2	S04

Number of Units in Package 2	28
Package 2 Height	11.811 in (30.000 cm)
Package 2 Width	15.748 in (40.000 cm)
Package 2 Length	23.622 in (60.000 cm)
Package 2 Weight	25.799 lb(US) (11.702 kg)
Unit Type of Package 3	P06
Number of Units in Package 3	112
Package 3 Height	29.528 in (75.000 cm)
Package 3 Width	23.622 in (60.000 cm)
Package 3 Length	31.496 in (80.000 cm)
Package 3 Weight	121.634 lb(US) (55.172 kg)

Offer Sustainability

California proposition 65	"WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov "
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.