

## Main

Product line	QO
Product type	Bar



## Complementary

Number of connectors	23
Wire size	AWG 14...AWG 4 copper AWG 12...AWG 4 aluminium
Provided equipment	2 screw
Bar length	8.11 in (206 mm)
Maximum length of segment	3.15 in (80 mm)
Device mounting	Direct mounting back of enclosure
Height	0.437 in (11.10 mm)
Depth	0.312 in (7.92 mm)
Tightening torque	30 lb.in Mounting screw 30 lb.in 20 lb.in, AWG 14...AWG 10, copper 20 lb.in, AWG 12...AWG 10, aluminium 35 lb.in, AWG 6...AWG 4 25 lb.in, AWG 8 25 lb.in, AWG 14...AWG 12, copper 25 lb.in, AWG 12...AWG 10, aluminium

## Ordering and shipping details

Category	00102 - QO LC ACCESSORIES
Discount Schedule	DE3A
GTIN	00785901026433
Nbr. of units in pkg.	1
Package weight(Lbs)	3.52 oz (99.79 g)
Returnability	Yes
Country of origin	US

## Packing Units

Unit Type of Package 1	PCE
Package 1 Height	0.40 in (1.016 cm)
Package 1 width	3.70 in (9.398 cm)
Package 1 Length	8.20 in (20.828 cm)
Unit Type of Package 2	PAL
Number of Units in Package 2	2100
Package 2 Weight	529.00 lb(US) (239.95 kg)
Package 2 Height	27.50 in (69.85 cm)

Package 2 width	40.00 in (101.6 cm)
Package 2 Length	48.00 in (121.92 cm)

### Offer Sustainability

California proposition 65	WARNING: Cancer and Reproductive Harm - <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>

### Contractual warranty

Warranty	18 months
----------	-----------