



## Main

Range	Mureva
Product or Component Type	Wander plug
Device short name	Mureva plug
Plug, socket category	Low voltage
Poles description	2P + E
Network type	AC
Outlet standard	Industrial

## Complementary

Plug, socket, control station shape	Straight
Line Rated Current	16 A
[Ue] rated operational voltage	200...250 V
Network Frequency	50/60 Hz
Ground lug clockwise position	6 h
Plug, socket material	Housing self-extinguishing engineering polymer
Contacts material	Sleeves brass
Connections - Terminals	Captive screws
Cable cross section	0.00...0.01 in <sup>2</sup> (1...4 mm <sup>2</sup> )
Cable outer diameter	0.31...0.59 in (8...15 mm)
Cable entry	Cable gland Fair lead
Thread type	Pg 16
Net Weight	0.32 lb(US) (0.144 kg)
Height	5.08 in (129 mm)
Width	2.87 in (73 mm)
Depth	2.87 in (73 mm)
Color	Gray RAL 7035)
Voltage colour	Blue

## Environment

Standards	IEC 60309-2 IEC 60309-1
IP degree of protection	IP67 conforming to IEC 60529
IK degree of protection	IK08 conforming to EN 62262
Fire resistance	1562 °F (850 °C) IEC 60695-2-11
Relative humidity	50 % 104 °F (40 °C) 70 % 86 °F (30 °C) 90 % 68 °F (20 °C)
Operating altitude	6561.68 ft (2000 m)
Ambient air temperature for operation	95 °F (35 °C) 86400 s ) -13...104 °F (-25...40 °C)

## Ordering and shipping details

Category	US10DE201078
Discount Schedule	0DE2
GTIN	3303432031947
Returnability	No
Country of origin	IT

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.80 in (7.100 cm)
Package 1 Width	2.80 in (7.100 cm)
Package 1 Length	5.55 in (14.100 cm)
Package 1 Weight	6.28 oz (178.000 g)
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	4.88 in (12.400 cm)
Package 2 Width	10.39 in (26.400 cm)
Package 2 Length	10.63 in (27.000 cm)
Package 2 Weight	3.92 lb(US) (1.780 kg)
Unit Type of Package 3	S03
Number of Units in Package 3	30
Package 3 Height	11.81 in (30.000 cm)
Package 3 Width	11.81 in (30.000 cm)
Package 3 Length	15.75 in (40.000 cm)
Package 3 Weight	12.65 lb(US) (5.740 kg)

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 <a href="#">Yes</a>
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations

## Contractual warranty

Warranty	18 months
----------	-----------