



Main

Range	Mureva
Product or Component Type	Wander plug
Device short name	Mureva plug
Plug, socket category	Low voltage
Poles description	3P + N + E
Network type	AC
Outlet standard	Industrial

Complementary

Plug, socket, control station shape	Straight
Line Rated Current	32 A
[Ue] rated operational voltage	380...415 V
Network Frequency	50/60 Hz
Ground lug clockwise position	6 h
Plug, socket material	Housing self-extinguishing engineering polymer
Contacts material	Sleeves brass
Connections - Terminals	Captive screws
Cable cross section	0.00...0.02 in² (2.5...10 mm²)
Cable outer diameter	0.45...0.83 in (11.5...21 mm)
Cable entry	Cable gland Fair lead
Thread type	Pg 21
Net Weight	0.55 lb(US) (0.25 kg)
Height	6.30 in (160 mm)
Width	4.02 in (102 mm)
Depth	4.02 in (102 mm)
Color	Gray RAL 7035)
Voltage colour	Red

Environment

Standards	IEC 60309-1 IEC 60309-2
IP degree of protection	IP67 conforming to IEC 60529
IK degree of protection	IK08 conforming to EN 62262
Fire resistance	1562 °F (850 °C) IEC 60695-2-11
Relative humidity	50 % 104 °F (40 °C) 70 % 86 °F (30 °C) 90 % 68 °F (20 °C)
Operating altitude	6561.68 ft (2000 m)
Ambient air temperature for operation	95 °F (35 °C) 86400 s) -13...104 °F (-25...40 °C)

Ordering and shipping details

Category	US10DE201078
Discount Schedule	0DE2
GTIN	3303432032340
Returnability	Yes
Country of origin	IT

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.13 in (10.500 cm)
Package 1 Width	4.13 in (10.500 cm)
Package 1 Length	6.69 in (17.000 cm)
Package 1 Weight	10.83 oz (307.000 g)
Unit Type of Package 2	BB1
Number of Units in Package 2	6
Package 2 Height	6.69 in (17.000 cm)
Package 2 Width	10.24 in (26.000 cm)
Package 2 Length	10.63 in (27.000 cm)
Package 2 Weight	4.48 lb(US) (2.030 kg)
Unit Type of Package 3	S03
Number of Units in Package 3	12
Package 3 Height	11.81 in (30.000 cm)
Package 3 Width	11.81 in (30.000 cm)
Package 3 Length	15.75 in (40.000 cm)
Package 3 Weight	9.95 lb(US) (4.512 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------