

# QO320SWN

Mini circuit breaker, QO, 20A, 3 pole,  
120/240VAC, 10kA, switch neutral, plug in  
mount



## Main

Product	Miniature circuit-breaker
Range	QO
Current Rating	20 A
Voltage Rating	120/240 V AC
Mounting Type	Plug-in
Number of Poles	3P
Circuit Breaker Type	Switch neutral
Ratings	Not rated
Electrical Connection	Pressure plate

## Complementary

Interrupt Rating	10 kA 120/240 V AC 50/60 Hz
Number of Panel Spaces	3
Wire Size	AWG 14...AWG 8 copper or aluminium
Tightening Torque	35.40 lbf.in (4 N.m)
Height	2.99 in (76 mm)
Width	2.24 in (57 mm)
Depth	2.91 in (74 mm)
Net Weight	0.85 lb(US) (0.386 kg)

## Environment

Certifications	UL Listed[RETURN]CSA
Ambient Rating	104 °F (40 °C)

## Ordering and shipping details

Category	US1DE2A00081
Discount Schedule	DE2A
GTIN	785901400707
Returnability	Yes
Country of origin	MX

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.50 in (8.89 cm)
Package 1 Width	3.70 in (9.398 cm)
Package 1 Length	2.20 in (5.588 cm)
Package 1 Weight	13.60 oz (385.554 g)

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Circularity Profile	No need of specific recycling operations
Halogen content performance	Halogen free product

## Contractual warranty

Warranty	18 months
----------	-----------