



Main

| | |
|----------------------|---------------|
| Product | Load Center |
| Marketing Trade Name | QO |
| Cover type | Surface cover |

Complementary

| | |
|--|---|
| Load Center Type | Main lugs |
| Line Rated Current | 200 A |
| Number of spaces | 30 |
| Short Circuit Current Rating | 65 kA |
| Maximum Number of Single Pole Circuits | 30 |
| Maximum Number of Tandem Breakers | 0 |
| Number of Phases | 3 phase |
| Voltage Rating | 208Y/120 V AC 240/120 V delta AC 240 V delta AC |
| Wire Size | AWG 6...300 kcmil aluminium/copper |
| Electrical Connection | Lugs |
| Grounding Bar | Grounding bar included (not installed) |
| Electrical connection | Lugs |
| Wiring configuration | 3-wire 4-wire |
| Busbar Material | Tin plated copper busbar |
| Enclosure Material | Welded galvanized steel |
| Cover Finish | Baked enamel grey |
| Box number | 6R |
| Height | 29.84 in (758 mm) |
| Width | 14.76 in (375 mm) |
| Tightening torque | 28.25 N.m (250 lbf.in) AWG 4...250 kcmil |

Environment

| | |
|---------------------------------------|---------------------------------|
| Enclosure Rating | NEMA 3R outdoor |
| Ambient air temperature for operation | 23 °F (-5 °C) 104 °F (40 °C) |
| Product certifications | UL listed |

Ordering and shipping details

| | |
|-------------------|------------------------------------|
| Category | 00017 - QO 3PH LOAD CENTER,OUTDOOR |
| Discount Schedule | DE3 |
| GTIN | 00785901295525 |
| Returnability | Yes |
| Country of origin | US |

Offer Sustainability

| | |
|----------------------------|---|
| California proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds which is known to the State of California to cause Carcinogen & Reproductive harm. For more information go to www.p65warnings.ca.gov |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |
| Circularity Profile | No need of specific recycling operations |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|