

## QOB220HID

Mini circuit breaker, QO, 20A, 2 pole,  
120/240VAC, 10kA, bolt on, high density  
discharge



### Main

Product	Miniature circuit-breaker
Range	QO
Current Rating	20 A
Voltage Rating	120/240 V AC
Mounting Type	Bolt-on
Number of Poles	2P
Circuit Breaker Type	High intensity discharge
Ratings	Not rated
Electrical Connection	Pressure plate

### Complementary

Interrupt Rating	10 kA 120/240 V AC
Number of Panel Spaces	2
Wire Size	AWG 14...AWG 8 copper or aluminium
Tightening Torque	35.40 lbf.in (4 N.m)
Height	2.99 in (76 mm)
Width	1.50 in (38 mm)
Depth	2.91 in (74 mm)
Net Weight	0.56 lb(US) (0.254 kg)

### Environment

Certifications	UL Listed[RETURN]CSA
Ambient Rating	104 °F (40 °C)

### Ordering and shipping details

Category	US10DE200015
Discount Schedule	0DE2
GTIN	785901362906
Returnability	Yes
Country of origin	MX

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.50 in (8.89 cm)
Package 1 Width	1.50 in (3.81 cm)
Package 1 Length	3.50 in (8.89 cm)
Package 1 Weight	8.96 oz (254.012 g)

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Cadmium and cadmium compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Circularity Profile	No need of specific recycling operations
Halogen content performance	Halogen free product

## Contractual warranty

Warranty	18 months
----------	-----------