



Main

Product	Miniature circuit-breaker
Range	QO
Current Rating	25 A
Voltage Rating	120/240 V AC 240 V AC 120 V AC
Mounting Type	Bolt-on
Number of Poles	2P
Circuit Breaker Type	Standard
Ratings	HACR rated
Electrical Connection	Pressure plate

Complementary

Interrupt Rating	22 KA 120/240 V AC 22 KA 240 V AC 22 kA 120 V AC
Number of Panel Spaces	2
Wire Size	AWG 14...AWG 8 copper or aluminium
Tightening Torque	40.71 lbf.in (4.6 N.m)
Height	2.99 in (76 mm)
Width	1.50 in (38 mm)
Depth	2.91 in (74 mm)
Net Weight	0.56 lb(US) (0.254 kg)

Environment

Certifications	UL Listed[RETURN]CSA
Ambient Rating	104 °F (40 °C)

Ordering and shipping details

Category	US10DE200015
Discount Schedule	0DE2
GTIN	785901371939
Returnability	Yes
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.60 in (4.064 cm)
Package 1 Width	3.50 in (8.89 cm)
Package 1 Length	3.50 in (8.89 cm)
Package 1 Weight	8.96 oz (254.012 g)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Circularity Profile	No need of specific recycling operations
Halogen content performance	Halogen free product

Contractual warranty

Warranty	18 months
----------	-----------