

Product data sheet

Characteristics

QOB2351021

Mini circuit breaker, QO, 35A, 2 pole,
120/240VAC, 10kA, bolt on, AC shunt



Main

Product	Miniature circuit-breaker
Range	QO
Current Rating	35 A
Voltage Rating	120/240 V AC 120 V AC
Mounting Type	Bolt-on
Number of Poles	2P
Circuit Breaker Type	Standard
Ratings	HACR rated
Electrical Connection	Box lugs
Options	Shunt trip 120/208/240 V AC

Complementary

Interrupt Rating	10 KA 120/240 V AC 10 kA 120 V AC
Number of Panel Spaces	3
Wire Size	AWG 8...AWG 2 copper or aluminium
Tightening Torque	44.25 lbf.in (5 N.m)
Height	3.11 in (79 mm)
Width	2.24 in (57 mm)
Depth	2.91 in (74 mm)
Net Weight	0.99 lb(US) (0.449 kg)

Environment

Certifications	UL Listed[RETURN]CSA
Ambient Rating	104 °F (40 °C)

Ordering and shipping details

Category	US10DE200015
Discount Schedule	0DE2
GTIN	785901703624
Returnability	No
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.23 in (5.662 cm)
Package 1 Width	2.92 in (7.412 cm)
Package 1 Length	3.37 in (8.565 cm)
Package 1 Weight	15.84 oz (449.056 g)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Circularity Profile	No need of specific recycling operations
Halogen content performance	Halogen free product

Contractual warranty

Warranty	18 months
----------	-----------