



Main

Marketing Trade Name	QO
Product Type	Load Center Cover

Complementary

Cover Type	Surface cover
Product Compatibility	For indoor load center
Surface Finish	Baked enamel Gray
Number of Spaces	30
Height	29.86 in (758.44 mm)
Width	14.25 in (361.95 mm)
Depth	0.7 in (17.78 mm)
Tightening Torque	Cover 2.3 N.m

Ordering and shipping details

Category	00001 - QO 1PH LC,12-42 CKT,NEMA1
Discount Schedule	DE3A
GTIN	00785901746034
Nbr. of units in pkg.	1
Package weight(Lbs)	9.05 lb(US) (4.105 kg)
Returnability	Yes
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	1.30 in (3.302 cm)
Package 1 width	14.60 in (37.084 cm)
Package 1 Length	30.10 in (76.454 cm)
Unit Type of Package 2	PAL
Number of Units in Package 2	81
Package 2 Weight	747.00 lb(US) (338.833 kg)
Package 2 Height	39.50 in (100.33 cm)
Package 2 width	40.00 in (101.6 cm)
Package 2 Length	48.00 in (121.92 cm)

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------