



### Main

|                             |                           |
|-----------------------------|---------------------------|
| Product or Component Type   | Miniature circuit-breaker |
| Range of Product            | QOU                       |
| Circuit breaker type        | Standard                  |
| Circuit breaker application | HACR rated                |

### Complementary

|                                |  |
|--------------------------------|--|
| Line Rated Current             | 40 A   |
| Electrical connection          | Slotted box lugs, line side<br>Slotted box lugs, load side |
| [Ue] rated operational voltage | 120/240 V AC<br>120 V AC<br>48 V DC                        |
| Mounting Mode                  | Unit mount   |
| AWG gauge                      | AWG 14...AWG 2 aluminium/copper                            |
| Height                         | 4.05 in (102.87 mm)  |
| Width                          | 1.5 in (38.10 mm)  |
| Depth                          | 2.95 in (74.93 mm)   |
| Tightening torque              | 45 lbf.in (5.08 N.m) (AWG 14...AWG 2)                      |

### Environment

|                        |                         |
|------------------------|-------------------------|
| Product Certifications | CSA<br>UL Listed<br>IEC |
|------------------------|-------------------------|

### Ordering and shipping details

|                   |                             |
|-------------------|-----------------------------|
| Category          | 00900-QOU BREAKERS & SWITCH |
| Discount Schedule | DE2                         |
| GTIN              | 785901585787                |
| Returnability     | No                          |
| Country of origin | MX                          |

### Packing Units

|                              |                      |
|------------------------------|----------------------|
| Unit Type of Package 1       | Db                   |
| Number of Units in Package 1 | 1                    |
| Package 1 Height             | 4.06 in (10.3 cm)    |
| Package 1 Width              | 1.50 in (3.8 cm)     |
| Package 1 Length             | 2.95 in (7.5 cm)     |
| Package 1 Weight             | 11.36 oz (322.051 g) |

## Offer Sustainability

|                             |   |
|-----------------------------|---|
| Sustainable offer status    | Green Premium product   |
| California proposition 65   | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |
| REACH Regulation            | <a href="#">REACH Declaration</a>   |
| EU RoHS Directive           | Compliant <a href="#">EU RoHS Declaration</a>   |
| Toxic heavy metal free      | Yes   |
| Mercury free                | Yes   |
| China RoHS Regulation       | <a href="#">China RoHS Declaration</a>  |
| RoHS exemption information  | <a href="#">Yes</a>   |
| Halogen content performance | Halogen free product  |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|