



Main

Product or Component Type	Miniature circuit-breaker
Range of Product	QOU
Circuit breaker type	Standard
Circuit breaker application	HACR rated
Type of Packing	Bulk

Complementary

Line Rated Current	100 A
Electrical connection	Slotted box lugs, line side Slotted box lugs, load side
[Ue] rated operational voltage	120/240 V AC 120 V AC 60 V DC
Mounting Mode	Unit mount
AWG gauge	AWG 12...AWG 2/0 aluminium/copper
Height	4.45 in (113.03 mm)
Width	0.75 in (19.05 mm)
Depth	2.95 in (74.93 mm)
Tightening torque	45 lbf.in (5.08 N.m) (AWG 12...AWG 2/0)

Environment

Product Certifications	CSA[RETURN]UL Listed[RETURN]IEC
------------------------	---------------------------------

Ordering and shipping details

Category	US10DE200900
Discount Schedule	ODE2
GTIN	785901188292
Returnability	No
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.0000000000 in (5.08 cm)
Package 1 Width	3.50 in (8.89 cm)
Package 1 Length	4.900 in (12.446 cm)
Package 1 Weight	14.720 oz (417.305 g)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Cadmium and cadmium compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Circularity Profile	No need of specific recycling operations
Halogen content performance	Halogen free product

Contractual warranty

Warranty	18 months
----------	-----------