

SC2040M125PF

All in one, Homeline, combination service entrance, ringed socket, 125A, semi flush, 20 spaces, 40 circuits, 10kA SSCR, OH, UG, no bypass, solar ready



Main

Product or Component Type	All-In-One
Range of Product	Homeline
Meter socket type	Ringed
Hub type	A-L

Complementary

Line Rated Current	125 A
Number of Phases	1 phase
Short-circuit current	22 kA
Mounting	Semi flush (outdoor)
Number of spaces	20
Number of circuits	40
Number of Tandem Breakers	20
Electrical connection	Lugs, line side Lugs, service ground
Wire Size	AWG 8...AWG 2/0 (aluminium/copper) service ground AWG 4...250 kcmil (aluminium/copper) line side
Tightening torque	Main lugs 250 lb.in, AWG 4...250 kcmil, aluminium/copper Service ground 50 lb.in, AWG 14...AWG 2/0, copper Service ground 50 lb.in, AWG 12...AWG 2/0, aluminium Branch lugs 50 lb.in, AWG 14...AWG 4, copper Branch lugs 50 lb.in, AWG 12...AWG 2, aluminium Branch lugs 35 lb.in, AWG 6...AWG 4, aluminium/copper Branch lugs 25 lb.in, AWG 8, aluminium/copper Branch lugs 20 lb.in, AWG 14...AWG 10, aluminium/copper Branch lugs 20 lb.in, AWG 12...AWG 10, aluminium/copper Cover 10 lb.in
Disconnect	Service disconnect (factory installed)
Disconnect Rating	125 A
Branch Breaker Rating	110 A
Service feed location	UG OH outdoor
Bypass type	No bypass
Connections - Terminals	Plug-on neutral
Color	Grey
Product Compatibility	Solar ready
Width	16.80 in (426.72 mm)
Depth	3.40 in (86.36 mm)
Height	39.80 in (1010.92 mm)
Bus Rating	225.0 A

Ordering and shipping details

Category	US1DE3A00148
Discount Schedule	DE3A
GTIN	785901903826
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.50 in (19.05 cm)
Package 1 Width	17.60 in (44.7 cm)
Package 1 Length	40.50 in (102.87 cm)
Package 1 Weight	54.90 lb(US) (24.902 kg)
Unit Type of Package 2	PAL
Number of Units in Package 2	10
Package 2 Height	40.00 in (101.6 cm)
Package 2 Width	42.00 in (106.68 cm)
Package 2 Length	48.00 in (121.92 cm)
Package 2 Weight	549.00 lb(US) (249.02 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations