

Product data sheet

Characteristics

SDSA1175CP

Surge protection device, Surgelogic, 36kA, 120/240 VAC, 1 phase, 3 wire, 25kA SCCR, NEMA 4X, consumer pack



Main

Product	Surge protection device
Range	Surgelogic

Complementary

Voltage Rating	120/240 V AC
MCOV	150 V
SCCR	25 kA
Surge Current	36 kA per phase
Nominal Discharge Current	10 kA
Number of Phases	1 phase
Wiring Configuration	3-wire
Local Signalling	Status LED green normal operation
Cable length	24 in (609.60 mm)
Height	2.25 in (57.15 mm)
Width	2.25 in (57.15 mm)
Depth	2.7 in (68.58 mm)

Environment

Ambient Operating	149 °F (65 °C)
Enclosure Rating	NEMA 4X
Enclosure Material	Black Plastic
Standards	UL 1449:ed. 4: type I NEC 285 CSA C22.2 No 8

Ordering and shipping details

Category	US1DE3A00102
Discount Schedule	DE3A
GTIN	785901038351
Returnability	No
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	16.00 oz (453.592 g)

EU RoHS Directive	Under investigation
-------------------	---------------------