

# SDSA1175T

Surge protection device, Surgelogic, 36kA, 120 VAC, 1 phase, 3 wire, 25kA SCCR, NEMA 4X



## Main

Product	Surge protection device
Range	Surgelogic

## Complementary

Voltage Rating	120 V AC
MCOV	150 V
SCCR	25 kA
Surge Current	36 kA
Nominal Discharge Current	10 kA
Number of Phases	1 phase
Wiring Configuration	3-wire
Connection	Wire
Local Signalling	Status LED
Cable length	24 in (609.60 mm)
Height	2.25 in (57.15 mm)
Width	2.25 in (57.15 mm)
Depth	1.935 in (49.15 mm)

## Environment

Enclosure Rating	NEMA 4X
Enclosure Material	Black Plastic
Standards	CSA C22.2 No 8 UL 1449:ed. 4

## Ordering and shipping details

Category	US1DE1B08462
Discount Schedule	DE1B
GTIN	785901984092
Returnability	Yes
Country of origin	FR

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.60 in (6.604 cm)
Package 1 Width	2.60 in (6.604 cm)
Package 1 Length	6.90 in (17.526 cm)
Package 1 Weight	10.56 oz (299.371 g)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>

Contractual warranty

Warranty	18 months
----------	-----------