



Main

Range of Product	Harmony XB5
Product or Component Type	Complete joystick controller
Device short name	XD2
Mounting diameter	0.87 in (22 mm)
Bezel material	Chromium plated metal

Complementary

[Ui] rated insulation voltage	500 V 3)EN/IEC 60947-1 600 V 3)UL 508 600 V 3)CSA C22.2 No 14
[Uimp] rated impulse withstand voltage	6 kV EN/IEC 60947-1
Operator position information	All positions
Notch per direction	2
Operator direction information	2 directions
Contacts type and composition	2 NO slow-break
Short-circuit protection	10 A gG (gl) Neozed cartridge fuse EN/IEC 60947-5-1
Connections - terminals	Captive screw clamp terminals, 1 x 0.5 mm ² Captive screw clamp terminals, 2 x 1.5 mm ² with or without cable end Faston connectors 6.3 mm
Electrical durability	1000000 Cycles, AC-15 230 V 3600 cyc/h 0.5 EN/IEC 60947-5-1 appendix C 1000000 Cycles, AC-15 127 V 3600 cyc/h 0.5 EN/IEC 60947-5-1 appendix C 1000000 Cycles, AC-15 24...48 V 3600 cyc/h 0.5 EN/IEC 60947-5-1 appendix C 1000000 Cycles, DC-13 24 V 3600 cyc/h 0.5 EN/IEC 60947-5-1 appendix C 1000000 Cycles, DC-13 48 V 3600 cyc/h 0.5 EN/IEC 60947-5-1 appendix C 1000000 cycles, DC-13 120 V 3600 cyc/h 0.5 EN/IEC 60947-5-1 appendix C
Electrical reliability	$\Lambda < 10\exp(-6)$
Contact code designation	A600-Q600
Overvoltage category	Class I IEC 61140
Mechanical durability	1000000 cycles
Fixing center	90 x 90 mm
Return	To 0 position
Height	5.71 in (145 mm)
Depth	2.36 in (60 mm)
Net Weight	1.10 lb(US) (0.5 kg)
[Ie] rated operational current	0.27 A 250 V, DC-13, Q300 EN/IEC 60947-5-1 3 A 240 V, AC-15, A300

Environment

Standards	EN/IEC 60947-5-1
Product Certifications	CSA[RETURN]LROS (Lloyds register of shipping)
Protective treatment	TC
Ambient Air Temperature for Storage	-40...158 °F (-40...70 °C)
Ambient air temperature for operation	-13...158 °F (-25...70 °C)

Vibration resistance	5 gn 40...500 Hz)IEC 60068-2-6
Shock resistance	20 gn IEC 60068-2-27

Ordering and shipping details

Category	US1000I22476
Discount Schedule	000I
GTIN	3389110611410
Returnability	Yes
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.62 in (9.2 cm)
Package 1 Width	3.62 in (9.2 cm)
Package 1 Length	5.71 in (14.5 cm)
Package 1 Weight	15.94 oz (452.0 g)
Unit Type of Package 2	S03
Number of Units in Package 2	18
Package 2 Height	11.81 in (30.0 cm)
Package 2 Width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	19.14 lb(US) (8.684 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------