

Main

Accessory / separate part type	Cable
--------------------------------	-------

Complementary

Accessory / separate part designation	Bare cable
Accessory / separate part category	Cabling accessories
Cable length	328.08 ft (100 m)
Material	PvR (PVC/NBR) sheath
Color	Matt black
Cable cross section	0.0008 in ² (0.5 mm ²)
Total number of wires	4
Wire insulation material	PVC
Flame retardance	Class C2 conforming to NF C 32-070
[Ue] rated operational voltage	300 V
[Ui] rated insulation voltage	2000 V NF C 32-201-1
Bending radius	Minimum 3 x external diameter
Tensile strength	10...35 N/mm ²
Hardness	70 shores A +/-5)
Net Weight	9.90 lb(US) (4.49 kg)

Environment

Ambient Air Temperature for Operation	-31...194 °F (-35...90 °C)
Ambient Air Temperature for Storage	-40...212 °F (-40...100 °C)
Environmental characteristic	Synthetic oils at 90 °C Mineral resistant at 90 °C Soluble resistant at 90 °C Without unmoulding agent



Ordering and shipping details

Category	US10DS222499
Discount Schedule	0DS2
GTIN	3389110197303
Returnability	No
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.921 in (12.500 cm)
Package 1 Width	9.843 in (25.000 cm)
Package 1 Length	9.843 in (25.000 cm)
Package 1 Weight	10.113 lb(US) (4.587 kg)
Unit Type of Package 2	S03
Number of Units in Package 2	2
Package 2 Height	11.8 in (30 cm)
Package 2 Width	11.8 in (30 cm)
Package 2 Length	15.7 in (40 cm)
Package 2 Weight	21.323 lb(US) (9.672 kg)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes

Contractual warranty

Warranty	18 months
----------	-----------