



Main

Range of Product	Easy Harmony XA2
Product or Component Type	Contact block
Device short name	ZA2E

Complementary

Contact operation	Slow-break
Contact block type	Single
Contacts usage	Standard contacts
Positive opening	Without
Mechanical durability	1500000 cycles
Connections - terminals	, <= 2 x 1.5 mm ² IEC 60947-1 , <= 1 x 2.5 mm ² IEC 60947-1 , >= 1 x 0.5 mm ² IEC 60947-1 Faston terminals 6.3 mm IEC 60947-1
Tightening torque	7.08 lbf.in (0.8 N.m)
Contacts material	Silver alloy (Ag/Ni)
Short-circuit protection	10 A fuse gL IEC 60269-1
[Ith] conventional free air thermal current	10 A IEC 60947-5-1
[Ui] rated insulation voltage	600 V 3)IEC 60947-1
[Uimp] rated impulse withstand voltage	6 kV IEC 60947-1
[Ie] rated operational current	2 A 230 V, AC-15, A600 IEC 60947-5-1 0.2 A 110 V, DC-13, Q600 IEC 60947-5-1
Electrical durability	500000 Cycles, AC-15, 2 A 230 V 60 cyc/mn 0.5 IEC 60947-5-1 500000 cycles, DC-13, 0.2 A 110 V 60 cyc/mn 0.5 IEC 60947-5-1
Contacts type and composition	1 NO

Environment

Protective treatment	TC
IP degree of protection	IP20 IEC 60529
Standards	IEC 60947-1 IEC 60947-5-4 IEC 60529 IEC 60947-5-1
Product Certifications	CE[RETURN]CCC
Ambient Air Temperature for Storage	-40...158 °F (-40...70 °C)
Ambient air temperature for operation	-13...131 °F (-25...55 °C)

Ordering and shipping details

Category	US1CP4B22153
Discount Schedule	CP4B
GTIN	3606480674143
Returnability	Yes
Country of origin	CN

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.43 in (1.1 cm)
Package 1 Width	3.23 in (8.2 cm)
Package 1 Length	3.94 in (10.0 cm)
Package 1 Weight	0.49 oz (14 g)
Unit Type of Package 2	S02
Number of Units in Package 2	200
Package 2 Height	5.91 in (15 cm)
Package 2 Width	11.81 in (30 cm)
Package 2 Length	15.75 in (40 cm)
Package 2 Weight	7.67 lb(US) (3.481 kg)
Unit Type of Package 3	PAL
Number of Units in Package 3	4000
Package 3 Height	23.62 in (60.0 cm)
Package 3 Width	31.50 in (80.0 cm)
Package 3 Length	35.43 in (90.0 cm)
Package 3 Weight	146.39 lb(US) (66.400 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes