

ZART06

Hand-held remote control, Harmony Pocket Remote, 6 single-step push buttons



Main

Range of Product	Harmony Pocket Remote
Product or Component Type	Hand-held remote control
Device short name	ZART
Control Button Type	6 single step push-button

Complementary

Material	Push-button cover silicone rubber Enclosure ABS + PET
Function Available	Power switch
Display type	1 LED
Operating Distance	50 m
Communication network type	Wireless
Transmission frequency	2.4 GHz
Maximum sensing distance	984.25 ft (300 m) in free field
Response time	< 500 ms
Autonomy	> 100 h with alkaline batteries
Battery type	2 AAA/LR3 alkaline
Width	2.60 in (66 mm)
Height	4.49 in (114 mm)
Depth	1.48 in (37.5 mm)
Net Weight	0.30 lb(US) (0.135 kg)

Environment

Radio agreement	IC FCC
IP degree of protection	IP67
Ambient air temperature for operation	-4...131 °F (-20...55 °C)
Ambient Air Temperature for Storage	-4...113 °F (-20...45 °C)
Operating altitude	0...6561.68 ft (0...2000 m)
Storage altitude	0.00...9842.52 ft (0...3000 m)
Relative humidity	0...95 % -4...140 °F (-20...60 °C) operating
Product Certifications	CE



Ordering and shipping details

Category	US10CS222467
Discount Schedule	0CS2
GTIN	3606481499479
Returnability	No
Country of origin	CN

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.77 in (4.5 cm)
Package 1 Width	2.95 in (7.5 cm)
Package 1 Length	5.31 in (13.5 cm)
Package 1 Weight	6.31 oz (179.0 g)
Unit Type of Package 2	S01
Number of Units in Package 2	8
Package 2 Height	5.91 in (15.0 cm)
Package 2 Width	5.91 in (15.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	3.66 lb(US) (1.658 kg)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Transmitter Dimensions

