

Product data sheet

Characteristics

3104140060

NEMA Motor Starter, Type S, replacement coil, 440/480VAC 50/60Hz, NEMA Size 00, 0 and 1 starters and 8903SM lighting



Main

Product or Component Type	Coil
Accessory / separate part destination	Class 8502 type SA (series A)/SB/SC contactor Class 8536 type SA (series A)/SB/SC starter Class 8903 type SM lighting contactor

Complementary

NEMA size	00 0 1
[Ue] rated operational voltage	480 V AC 60 Hz 440 V AC 50 Hz
Inrush power in VA	232 VA 245 VA
Average consumption	27 VA 26 VA
Height	2.15 in (54.7 mm)
Width	3.21 in (81.5 mm)
Depth	1.90 in (48.3 mm)

Ordering and shipping details

Category	18079-SPARE PARTS DISCOUNT CP10
Discount Schedule	CP10
GTIN	785901093138
Returnability	No
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.10 in (5.334 cm)
Package 1 Width	2.80 in (7.112 cm)
Package 1 Length	3.40 in (8.636 cm)
Package 1 Weight	6.88 oz (195.045 g)

Offer Sustainability

EU RoHS Directive	Not applicable, out of EU RoHS legal scope
-------------------	--

Contractual warranty

Warranty	18 months
----------	-----------