

Product data sheet

Characteristics

3107440038

NEMA Motor Starter, Type S, replacement coil, 110/120VAC 50/60Hz, 2 or 3 pole, NEMA size 3 starter and 8903SQ lighting



Main

Product or Component Type	Coil
Accessory / separate part destination	Class 8502 type SE contactor Class 8903 type SQ lighting contactor Class 8910 type DPA12/SYD138 contactor

Complementary

NEMA size	3
[Ue] rated operational voltage	120 V AC 60 Hz 110 V AC 50 Hz
Inrush power in VA	700 VA 678 VA
Average consumption	46 VA 47 VA
Height	2.87 in (73 mm)
Width	2.56 in (65 mm)
Depth	0.08 in (2.093 mm)

Ordering and shipping details

Category	18079 - SPARE PARTS DISCOUNT CP10
Discount Schedule	CP10
GTIN	785901110903
Nbr. of units in pkg.	1
Package weight(Lbs)	13.44 oz (381.018 g)
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	2.10 in (5.334 cm)
Package 1 width	2.80 in (7.112 cm)
Package 1 Length	3.30 in (8.382 cm)
Unit Type of Package 2	CAR
Number of Units in Package 2	20
Package 2 Weight	17.21 lb(US) (7.806 kg)
Package 2 Height	3.10 in (7.874 cm)
Package 2 width	4.20 in (10.668 cm)
Package 2 Length	13.10 in (33.274 cm)

Offer Sustainability

EU RoHS Directive	Not applicable, out of EU RoHS legal scope
-------------------	--

Contractual warranty

Warranty	18 months
----------	-----------
