



Main

Product	Double Throw Safety Switch
Duty Rating	General duty
Disconnect Type	Non-fusible disconnect
Factory Installed Neutral	None
Number of Poles	3
Current Rating	200 A
Voltage Rating	480 V AC 250 V DC
Enclosure Rating	NEMA 1
Motor power hp	15 hp at 480 V AC 50-60 Hz for 3 phase motors

Complementary

Short-circuit current	10 kA H or J
Fuse type	H or J
Mounting Type	Surface
Wire Size	AWG 6...300 kcmil copper or aluminium
Tightening torque	340 lbf.in (38.4 N.m) (AWG 6...300 kcmil)
Depth	11.75 in (298.45 mm)
Width	23.88 in (606.55 mm)
Height	30.88 in (784.35 mm)
Net Weight	64.07 lb(US) (29.06 kg)

Environment

Certifications	UL Listed
----------------	-----------

Ordering and shipping details

Category	US10DE100033
Discount Schedule	0DE1
GTIN	785901453772
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	12.0000000000 in (30.48 cm)
Package 1 Width	24.50 in (62.23 cm)
Package 1 Length	32.0000000000 in (81.28 cm)
Package 1 Weight	62.739 lb(US) (28.458 kg)
Unit Type of Package 2	PAL
Number of Units in Package 2	6
Package 2 Height	40.0000000000 in (101.6 cm)
Package 2 Width	40.0000000000 in (101.6 cm)

Package 2 Length	48.0000000000 in (121.92 cm)
Package 2 Weight	376.773 lb(US) (170.901 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------