



Main

Range of Product	Harmony 9001K
Product or Component Type	Head for selector switch
Device short name	K
Type of operator	maintained
Operator profile	Black standard knob

Complementary

Bezel material	Metal
Mounting diameter	1.2 in (30 mm)
Operator position information	2 positions
Contacts type and composition	Without contact block
Device presentation	Basic element
Cap/operator or lens colour	Black
Operator profile	Standard handle
Type of operator	Stay put
Size	30 mm
Cam profile	5

Environment

NEMA degree of protection	NEMA 1/2/3/3R/4/6/12/13
Product Certifications	UL listed file E42259 CCN NKCR[RETURN]CE[RETURN]CSA LR24590 class 3211 03

Ordering and shipping details

Category	US10CS121426
Discount Schedule	OCS1
GTIN	785901322832
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.0000000000 in (5.080 cm)
Package 1 Width	2.300 in (5.842 cm)
Package 1 Length	2.800 in (7.112 cm)
Package 1 Weight	4.339 oz (123.000 g)
Unit Type of Package 2	S02
Number of Units in Package 2	28
Package 2 Height	5.906 in (15.000 cm)
Package 2 Width	11.811 in (30.000 cm)

Package 2 Length	15.748 in (40.000 cm)
Package 2 Weight	8.225 lb(US) (3.731 kg)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------