

# Product data sheet

## Characteristics

# EZM314125

Branch unit, EZ Meter-Pak, 125A, 4 sockets, 208Y/120VAC, no bypass, ringed, 800A busbar



### Main

Product	Meter Center Branch Unit
Current Rating	125 A
Type	Meter-Pak
Bus Rating	800 A
Number of Jaws	5 without jaw release
Number of Meter Sockets	4
Bypass Type	No bypass
Socket Type	Ringed

### Complementary

Certifications	UL Listed
Busbar Material	Aluminium busbar
Enclosure Material	Steel
Enclosure Rating	NEMA 3R
Maximum Voltage Rating	208Y/120 V AC
Mounting	Surface
Phase	3 phase in 1 phase out
Wire Configuration	4-wire
Height	48.11 in (1222 mm)
Width	12.24 in (311 mm)
Depth	7.09 in (180 mm)
Net Weight	60.41 lb(US) (27.400 kg)

### Ordering and shipping details

Category	00020-EZ METER-PAK
Discount Schedule	DE4
GTIN	785901402121
Returnability	Yes
Country of origin	MX

### Packing Units

Unit Type of Package 1	Db
Number of Units in Package 1	1
Package 1 Height	8.82 in (22.4 cm)
Package 1 Width	14.69 in (37.3 cm)
Package 1 Length	49.02 in (124.5 cm)
Package 1 Weight	66.52 lb(US) (30.173 kg)

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>

## Contractual warranty

Warranty	18 months
----------	-----------